

Die, HSS G right, tol. A with spiral point and 1.75 thread chamfer

for universal use up to 700 N/mm²

ORION[®]

Application:

For cutting G (pipe) threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm².

Execution:

- right die, tol. A with spiral point and 1.75 pitch

Advantage:

- standard geometry with excellent price/performance ratio

Art. no.	13487 050
Brand	ORION
Manufacturer Part Number	13487050
Thread type	Pipe thread
Cutting material	HSS
Tolerance of dies	A
Thread type x nominal diameter in inches	G 5/8 in
Number of thread starts per inch	14
Outer diameter	55 mm
Height	16 mm
Cutting direction	Right-hand cutting
Gross Weight	0.179 kg
Product Group	1DC



EAN

4039247074778