

500 series shelf trolley, load capacity 500 kg

In 2 sizes and with 5 load areas



Application:

Ideal as a transport and picking trolley for many different types of goods.

Execution:

- Electrolytically galvanised, highly stable tubular frame structure
- Load areas made of MDF board
- Fixed handle at a height of 1040 mm
- 300 mm spacing between the load area rails

Advantage:

- Helps to transport goods more efficiently
- Runs very smoothly even under heavy load



Art. no.	50250 045
Brand	KONGAMEK
Manufacturer Part Number	KM538-3B
Load-carrying capacity	500 kg
ESD-capable	No
Load-carrying capacity of loading surfaces	100 kg
Colour	Silver coloured
Material of loading surface	Medium density fibreboard
Number of loading surfaces	5
Loading-surface width	800 mm
Length	1200 mm
Width	800 mm
Height	1800 mm
Length x width x height	1200 x 800 x 1800 mm
Surface	Zinc plated
Made in	Sweden
With wheel lock	Yes
Wheel diameter	200 mm
Material of wheel	Solid rubber
Wheel width	50 mm
Number of fixed rollers	2
Number of steering rollers	2
Gross Weight	87.500 kg
Product Group	5AT

EAN

7350050357702