



Finish : HeLeN

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES 9245 498 45500 0833/000 p.190-1 Of 26/11/2003		HALOGEN LAMP INFRARED HeLeN 15030R 1500W 240V						9245 498 45500 0833/000			31/01/2011				
REF. : PDM IRK 2010-053		DOCUMENTATION		UNIT mm	PROJ. EUROP 	2 SH		SH	190-1	10	SCA. 1	A4			
NAME : J.P. CHARLIER		VALIDATION : A. PICHARD			DR. FISCHER Europe										
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															

PRODUCT REQUIREMENT SHEET

See LV 75-032

MEASURING VOLTAGE	240V (stabilisation 3 min.)
MEASURING POSITION	Horizontal
LIFE TEST POSITION	Horizontal
BURNING POSITION	P15
SWITCHING CYCLE	Continuous
AGEING	1h at rated voltage

		VALUE UNIT	TOLERANCE
WATTAGE		1500W	± 6 %
LIFE		5000 h	average
COLOR TEMPERATURE	Clear lamp HeLeN Lamp	2300 K NA	± 100 K
FLUX (HeLeN lamp)	Clear lamp Reduction	10000 lm 95 %	Indicative value min
WEIGHT		34 g	

1	0833	2	0833	3	0000	4		5		6		7		8	
SUPERSEDES :		HALOGEN LAMP						9245 498 45500		27/10/2011					
9245 498 45500		INFRARED HeLeN						0833/000							
0833/000 p. 190-2		15030R 1500W 240V													
Of 31/01/2011		REF. : PDM IRK 2011-016		DOCUMENTATION		UNIT	mm	PROJ EUROP	2	SH	SH	190-2	10		A4
NOM : J.P. CHARLIER		VALIDATION : A. PICHARD						DR. FISCHER Europe							
All rights reserved. Reproduction in whole or in part is prohibited without the written consent of the copyright owner.															