

## 64333 B 40-15

Halogen lamps with reflector, current-controlled, 30...40 W



### Product family benefits

- Reduced operation and maintenance costs due to long lifetime
- Instant and constant light output over the lamp life
- Flicker-free operation
- Mercury-free

### Product family features

- Dimmable
- Available with connector combinations A, B, C/Z on request
- Infrared radiation output that provides light in the worst of conditions



## Product datasheet

### Technical data

#### Product information

Order reference	64333
-----------------	-------

#### Electrical data


Lamp current	6.6 A
Nominal wattage	40.00 W

#### Photometrical data

Luminous intensity	10000 cd <sup>1)</sup>
Axial luminous intensity	12700 cd

<sup>1)</sup> Minimum

#### Dimensions & weight



Diameter	50.4 mm
Length	48.0 mm
Length with base excl. base pins/connection	37.00 mm

#### Lifespan

Lifespan	1500 h
----------	--------

#### Capabilities

Dimmable	Yes
Burning position	h45
Connection with cable	Yes
Mains terminals	Leads w/female round connectors

#### Country specific categorizations

## Product datasheet

<b>Order reference</b>	64333
------------------------	-------

---

### Country specific information

<b>Product code</b>	<b>METEL code</b>	<b>SEG-No.</b>	<b>STK-Number</b>	<b>UK Org</b>
4008321104731	OSRH64333B	-	-	-
4008321104731	OSRH64333B	-	-	-

## Product datasheet

---

### Safety advice

To prevent personal injury or damage to property, halogen lamps may only be operated in suitable luminaires designed with suitable mechanisms (protective shields, grids, etc.) to ensure that in the event of a lamp bursting no parts/shards can escape and that during operation no ultraviolet radiation can escape. There must also be a warning sign to indicate that the lamps give off high levels of heat. Detailed information is available on request.

---

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321104731	64333 B 40-15	Folding carton box 1	50 mm x 34 mm x 34 mm	0.06 dm <sup>3</sup>	19.00 g
4008321104748	64333 B 40-15	Shipping carton box 20	191 mm x 130 mm x 83 mm	2.06 dm <sup>3</sup>	448.00 g

---

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

### References / Links

For more information on airfield lamps see the brochure:

"The reliable guiding stars - Effective solutions for airfield lighting: Tungsten halogen lamps and LED light sources".

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

---