

M12 Polyamide (PA) Gland Light Grey (3-5mm)



Basic data:

ID	0004410006
GTIN	7630268414931



Features:

Nylon cable gland M12 with lock nut light grey

Technical data:

Thread type:	Metric
Nominal thread size metric/PG:	12
Pitch thread:	1.5 mm
Thread length:	9 mm
Wrench width:	16 mm
Hexagon angular dimension:	18 mm
Suitable for cable diameter:	3 ... 5 mm
Material:	Plastic
Material quality:	Polyamide (PA)
Surface protection:	Untreated
Halogen free:	Yes
Degree of protection (IP):	IP68
Shock resistant:	Yes
Colour:	Light grey
RAL-number:	7035
With locknut:	Yes
Model:	Straight
With strain relief:	Yes
Type of sealing:	Sealing ring
Operating temperature:	-40 ... 100 °C (static)