




FT-00-PPV-M6

Fibre optics



Product characteristics
Diffuse reflection sensor

M6

Amplifier Range

OKF 20 mm

OUF 20 mm

OOF 220 mm

Range

Range

OKF: 20 mm / OUF: 20 mm / OOF: 220 mm

Environment

Ambient temperature [°C]

-20...80

Mechanical data

Design

straight

Length [mm]

600

Min. bending radius [mm]

10

Fiber arrangement



Fibre optic

PMMA

Sensing head

stainless steel (303S22)

Sheathing

PU (polyurethane); adapter: ABS

Weight [kg]

0.047

Accessories

Accessories (included)

2 hexagon nuts; M6; stainless steel; 2 tooth lock washers; 1 knurled nut; M11

Remarks

Pack quantity [piece]

1