

Product characteristics

Jumper

M8-plug / M12-socket

Free from silicone

Free from halogen

Gold-plated contacts

Electrical data

Electrical design

DC PNP

Operating voltage [V]

10...36 DC

Current rating [A]

3

Protection class

III

Environment

Ambient temperature [°C]

-25...90, cULus: max. 75 °C

Ambient temperature (moving) [°C]

-25...90, cULus: max. 75 °C

Protection

IP 65 / IP 67 / IP 68 / IP 69K

Tests / approvals

MTTF [Years]

20027

Mechanical data

Design

angled / angled

Material body

housing connector: TPU orange; housing socket: TPU black transparent; sealing: Viton

Material nut

Brass; nickel-plated

Tightening torque for knurled nut [Nm]

plug: 0.3...0.5 \*) / socket: 0.6...1.5

Drag chain suitability

Bending radius for flexible applications: min. 10 x cable diameter  
max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s<sup>2</sup>  
Travel speed: 5 m/s<sup>2</sup>  
Bending cycles: > 5 million  
Torsional strain: ± 180 °/m

Weight [kg]

0.036

Displays / operating elements

Output status indication LED

yellow

Operation LED

green

Electrical connection

Connection




PUR cable / 0.3 m;  
3 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm); Ø 4.9 mm; halogen-free

Sheath colour

black

**Wiring**

EVC373 - Jumper - eclass: 27279201 / 27-27-92-01



Remarks

Remarks

\*) Take into account the maximum value of the counterpart!

Pack quantity

[piece]

1