

## PROFIBUS-PLUG-MALE (SUB-D) 180°

Cut clamp for rigid wire

Bus Connection Plug 180°  
SUB-D9 (male), IDC terminals, rigid cable  
PROFIBUS

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Technical Data

Operating voltage	via the fieldbus device; 4.75...5.25 V DC
Terminating resistor	integrated, switchable
Current consumption	max. 12.5 mA
Transfer rate	to 12 Mbit/s

#### General data

Protection	IP20
Connection	PROFIBUS, FC-cable rigid, 1 × 2 × 0.64 mm, for outer diameter 8.0 ± 0.5 mm
Dimensions H × W × D	72×35×17 mm
Temperature range	0...+60 °C (storage temperature -25...+80 °C)

**Commercial data**

country of origin	DE
customs tariff number	85389091
minimum order quantity	1