

**M8 FEMALE FLANGE PLUG REAR MOUNT**

TPE wires 3x0.25 1m

Flange M8 female


4-pole

3-pole


Rear mounting

Mounting nut



with multi-strand wire

[Link to Product](#)**Illustration**


Female



stay connected



Female



Product may differ from Image

**Form**

08575

**Technical Data**

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing

Protection IP67 inserted and tightened (EN 60529)

### Cables

Cable number	970
No./diameter of wires	3 × 0.25 mm <sup>2</sup>
Wire isolation	PP (br, bk, bl)
Shore hardness outer jacket	70 ± 5D
Outer diameter	approx. 1.25 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

### General data

Temperature range -25...+85 °C

### Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1