4-2363962-0 ✓ ACTIVE

TE Internal #: 4-2363962-0 PCB Mount Header, Vertical, Board-to-Board, 40 Position, .4mm [. 015in] Centerline, Gold, Printed Circuit Board, .5A Contact Current Rating (Max)

View on TE.com >



Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles



PCB Connector Assembly Type: PCB Mount Header

PCB Mount Orientation: Vertical

Connector System: Board-to-Board

Number of Positions: 40

Centerline (Pitch): .4 mm [.015 in]

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Configuration Features	
PCB Mount Orientation	Vertical
Number of Positions	40
Board-to-Board Configuration	Parallel
Electrical Characteristics	
Dielectric Withstanding Voltage (Max)	250 VAC
Operating Voltage	60 VAC
Body Features	
Connector Profile	Low
Contact Features	

4-2363962-0

PCB Mount Header, Vertical, Board-to-Board, 40 Position, .4mm [.015in] Centerline, Gold, Printed Circuit Board, .5A Contact Current Rating (Max)



Contact Layout	Inline
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.1 μm[4 μin]
Contact Type	Pin
Contact Current Rating (Max)	.5 A
Termination Features	
Termination Method to Printed Circuit Board	Surface Mount
Mechanical Attachment	
Mating Alignment	With
Mating Alignment Type	Polarized
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Housing Features	
Centerline (Pitch)	.4 mm[.015 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic
Dimensions	
Row-to-Row Spacing	.88 mm[.034 in]
Stack Height	.8 mm[.031 in]
Usage Conditions	
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

4-2363962-0

PCB Mount Header, Vertical, Board-to-Board, 40 Position, .4mm [.015in] Centerline, Gold, Printed Circuit Board, .5A Contact Current Rating (Max)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-

Compatible Parts



Customers Also Bought

4-2363962-0

PCB Mount Header, Vertical, Board-to-Board, 40 Position, .4mm [.015in] Centerline, Gold, Printed Circuit Board, .5A Contact Current Rating (Max)





Documents

Product Drawings 0.4mm BTB CONN H0.8 PLUG ASSEMBLY, 40P

English

CAD Files

3D PDF

3D

Customer View Model ENG_CVM_CVM_4-2363962-0_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2363962-0_1.3d_igs.zip

English

Customer View Model

```
ENG_CVM_CVM_4-2363962-0_1.3d_stp.zip
```

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Application Specification

English