

NYS372P

Phono cable jack, nickel plated shell and contacts



Technical Information

Product

Title	NYS372P
--------------	---------

Electrical

Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector

Mechanical

Cable O.D.	7.2 mm
Lifetime	> 1000 mating cycles
Wiresize	
Wiresize	26 AWG

Material

Contact plating	Nickel
Contacts	Brass (CuZn39Pb3)
Shell	Brass (CuZn39Pb3)
Shell plating	Nickel
Strain relief	SnCe plated, crimp type
Insulation	Thermoplastic

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C