

SCLC mini boring bar, offset, HSS, positive, right-hand

For face and longitudinal turning with CC indexable insert

ATORN[®]

Application


For face and longitudinal turning with CC indexable insert 80°.

Version

- Precision-made boring bar, **HSS**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive body geometry ensures low cutting forces
- Very high rigidity and very good cut quality due to HSS base material



Art. No.	17846 310
ISO name	AH 0610 H SCLC R/L 03
Min. bore diameter	7 mm
Tapered diameter	6 mm
Shaft diameter	10 mm
Clearance length	24 mm
Length	100 mm
Clamping surface height	9 mm
Programming size	2.5 mm
Suitable for indexable inserts	CC.. 03..
Tool design	Right
DIN	8024

EAN-Code

4050293344271