

XBO 2000 W/HS OFR

XBO | Xenon short-arc lamps 450...10,000 W



Areas of application


- Classic 35 mm film projection
- Digital film and video projection
- Architectural and effect light ("Light Finger")
- Sunlight simulation

Product benefits

- Short arc with very high luminance for brighter screen illumination
- Constant color temperature of 6,000 K throughout the entire lamp lifetime
- Easy to maintain
- High arc stability
- Instant light on screen thanks to hot restart function
- Wide dimming range

Product features

- Color temperature: approx. 6,000 K (Daylight)
- Wattage: 1,200...8,000 W
- Very good color rendering index: $R_a >$




Product datasheet

Technical data

Electrical data

Nominal wattage	2000.00 W
Lamp voltage	27 V
Nominal current	85.0 A
Lamp current	85.0 A

Dimensions & weight



Diameter	60.0 mm
Length	302.0 mm
Product weight	495.00 g

Additional product data

Base anode (standard designation)	SK27/50
Base cathode (standard designation)	SFcX27-8
Product remark	H = Suitable for horizontal burning position/S = Short

Capabilities

Burning position	h90
------------------	-----

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321081360	OSRXBO2000HSOFR	-	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321081360	XBO 2000 W/HS OFR	Shipping carton box 1	500 mm x 200 mm x 204 mm	20.40 dm ³	1247.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.