

No.	Length mm	Head width mm	Finish	Cutting capacity			Weight g
				Wire soft	mm medium	Ø hard	

End cutters

with slim, pointed head, special fl at cutting edge and adjustable stop screw

3-981-15	135	10	ultra flush	0.8	0.6	-	80
----------	-----	----	-------------	-----	-----	---	----



3-981-15



3-985-15

Oblique top cutters

Cutting surface angled by 35 °, for flush cutting, for horizontal and vertical use.

3-985-15	130	10	flush	1.2	1.0	-	75
----------	-----	----	-------	-----	-----	---	----



3-999

Wire lead catcher for side cutters (to retrofit)

3-999-1	3-961-15 to 3-969-15 (10 mm head width)						9
3-999-2	3-971-15 to 3-973-15 (12.5 mm head width)						9

GRIPPING PLIERS

Round nose pliers

extremely slim

3-991-15	130	10	short plain jaws				75
----------	-----	----	------------------	--	--	--	----



3-992-15



3-991-15

Flat nose plier

extremely slim

3-992-15	130	10	short plain jaws				75
----------	-----	----	------------------	--	--	--	----

Snipe nose plier

extremely slim

3-996-15	140	10	short plain jaws				80
----------	-----	----	------------------	--	--	--	----



3-996-15

NEW



3-960 VT
6-pcs. set consisting of:

4 pliers from the TECHNICline series
2 ESD Tweezers

lined up on the ESD tool holder VARIO
for mounting or hanging

Content: Side cutters Art. No. 3-963-15, End cutters Art. No. 3-981-15,
Flat nose pliers Art. No. 3-992-15, Snipe nose pliers Art. No. 3-996-15,
2 ESD Tweezers, straight Art. No. 5-055-13 and curved Art. No. 5-078-13



3-960 VT