


pH and ORP Electrodes

 **Choice of Standard or Specialized electrodes**
BNC connector for use with virtually any pH/ORP meters

Features:

- All electrodes are Ag/AgCl gel filled (fast response: 95% in 5sec)
- Include 39" (1m) cable with BNC connection and storage solution bottle (601500, 601100, and 67500B) or cap (60120B). Six month warranty

General purpose pH/Ref electrodes 60120B and 601500:

- Rugged, polycarbonate construction features glass pH sensing bulb surrounded by protective teeth. pH range (0 to 14pH), operating temperature (0 to 80°C). Choice of Mini or Standard size.

Flat surface electrode (Easy-to-clean) 601100:

- PVC bodied electrode, ideal for pH of solid products with minimal moisture like cheese, soils or electrophoretic/agar gels. pH range (0 to 14pH), operating temperature (5 to 80°C).

Redox ORP/Ref electrode 67500B:

- Platinum sensing surface, polycarbonate body and sealed reference



60120B - Mini size



601500 - Standard size



601100 - Flat Surface



67500B - ORP Electrode



Ordering Information:

- 60120BMini Electrode (10 x 120mm)
601500Standard pH Electrode (12 x 160mm)
601100Flat Surface Electrode (15 x 106mm)
67500BORP Electrode (13 x 154mm)