

Han-Eco cable gland M32



Part number	19 41 000 5131
Specification	Han-Eco cable gland M32
HARTING eCatalogue	https://b2b.harting.com/19410005131

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Accessories
Series of hoods/housings	Han-Eco [®]
Type of accessory	Cable gland

Technical characteristics

Tightening torque	15 Nm Fitting 4 Nm Cap nut
Wrench size	36
Limiting temperature	-40 +125 °C
Size	M32
Clamping range	13 21 mm

Material properties

Material (cable glands)	Polyamide (PA)
Colour (accessories)	RAL 9005 (jet black)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)

Product data sheet 19 41 000 5131 Han-Eco cable gland M32



Material properties

Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)
Commercial data	
Packaging size	2
Net weight	33.32 g
Country of origin	Germany
European customs tariff number	39174000
GTIN	5713140130524
eCl@ss	27140801 Screwed cable gland (electrical)

Page 2 / 2 | Creation date 2023-02-14 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany