



ecobasic LED A60 E27 240V 10W 2700K Opal

Item no. 80100038991

Bailey ecobasic LED Lamp GLS A60 E27 (ES) 10W Warm White 2700K CRI80-89 Opal
806lm 220-240V AC 270D 60x110mm

Specifications

Product group	LED lamp
Brand	Bailey
Serie	ecobasic
Part no. brand	80100038991
Lamp shape	GLS
Base	E27
Finish	Opal
Nominal voltage (V)	220
Nominal voltage upper limit (V)	240
Nominal power (W)	10
Nom. Stroom (mA)	87
Luminous flux (lm)	806
Colour	Warm White
Colour temperature (K)	2700
Colour rendering index CRI	80-89
Colour code	827
Dimmable	No
Lifespan (h)	20000
Beam angle (°)	270
Degree of protection (IP)	IP20
Energy efficiency class	A+
Diameter (mm)	60
Length (mm)	110
EAN-code Bailey	8714681389911