

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

CABLE

Shielded cable with PVC sheath, bend radius in fixed position ≥ 50 mm.

CONNECTORS

Male and female SMA connectors.

APPLICATIONS


If the extension is used as a spare part in an existing equipment, please contact the EleSa technical service to check its compatibility.

SPECIAL EXECUTIONS ON REQUEST

Extensions with cables in different lengths.



Mechanical and electrical characteristics	
Impedance	50 Ohm
Working temperature	-40 °C + 70 °C



Position indicators

Code	Description	L \pm 50	d \pm 0.5	Δ
CE.99253	FC-UC-1.0	1000	3	48
CE.99255	FC-UC-2.5	2500	5	106
CE.99257	FC-UC-5.0	5000	5	208
CE.99259	FC-UC-10.0	10000	5	206