

Part no.: 50106881
KB-ROD4 plus-5000
Interconnection cable





Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Connection	
Connection 1	
Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Design	Axial
Connection 2	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Cable properties	
Shielded	Yes
Cable design	Interconnection cable
Cable length	5,000 mm
Sheathing material	PUR

Classification	
Customs tariff number	85444290
eCl@ss 8.0	27069190
eCl@ss 9.0	27069190
ETIM 5.0	EC001578
ETIM 6.0	EC001578

Electrical connection

Connection 1	
Type of connection	Sub-D
Type	Female
No. of pins	9 -pin
Design	Axial

Connection 2	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking