

## CUBE67 ACCESSORIES

System interface connector

M12

Female straight

Internal system connection

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Technical Data

Operating voltage	24 V DC
Operating current	max. 4 A
Mating cycles	min. 500

#### General data

Protection	IP65
Dimensions H x W x D	80.5x34x32 mm
Connection	Female M12, 6-pole, Han-Brid® 6-pole
Temperature range	-40...+85 °C

#### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1