


40aLSP Sockets

HPQ

- for external spline-drive screws
- long, extra deep bolt clearance
- MS-33787, MIL-W-8982
- HPQ® high performance steel, chrome plated



Code	Spline size	"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	Δg	g	
01021007	7	7/32	8.6	10.7	5	50.8	6	42.8	18	1	
01021008	8	1/4	9.5	10.7	5.6	50.8	8	42.8	24	1	
01021010	10	5/16	11.6	11.6	7.1	50.8	8	40.8	27	1	

402aSP Uniflex sockets

HPQ

- for external spline-drive screws
- MS-33787, MIL-W-8982
- HPQ® high performance steel, chrome plated



Code	Spline size	"	d ₁ mm	d ₂ mm	d ₃ mm	L mm	t ₁ mm	t ₂ mm	Δg	g	
01542016	8	1/4	9.5	12.7	5.6	32	6.4	9.8	16	5	
01542020	10	5/16	11.6	12.7	7.1	35	8	13	18	5	

41K Screwdriver sockets


- for slotted screws
- blades to DIN 5264
- Chrome Alloy Steel, chrome plated



Code	mm	L ₁ mm	L ₂ mm	d mm	a mm	b mm	Δg	g	
01280006	0.6x3.5	28	16	11.6	0.6	3.5	10	5	
01280008	0.8x4	28	16	11.6	0.8	4	10	5	
01280010	1x5.5	28	16	11.6	1	5.5	11	5	
01280012	1.2x8	28	16	11.6	1.2	8	12	5	

44 INHEX sockets

- for socket head screws
- DIN 7422
- Chrome Alloy Steel, chrome plated



Code	mm	L ₁ mm	L ₂ mm	d mm	Δg	g	
01050003	3	55	30	10.7	20	5	
01050004	4	55	30	10.7	20	5	
01050005	5	55	30	10.7	25	5	
01050006	6	55	30	11.6	30	5	

44a INHEX sockets

- for socket head screws
- DIN 7422
- Chrome Alloy Steel, chrome plated

Code	"	L ₁ mm	L ₂ mm	d mm	Δg	g	
01450004	1/16	55	30	10.7	11	5	
01450005	5/64	55	30	10.7	12	5	
01450006	3/32	55	30	10.7	14	5	
01450007	7/64	55	30	10.7	17	5	
01450008	1/8	55	30	10.7	12	5	
01450009	9/64	55	30	10.7	13	5	
01450010	5/32	55	30	10.7	14	5	
01450012	3/16	55	30	10.7	17	5	
01450014	7/32	55	30	10.7	19	5	
01450016	1/4	55	30	11.6	24	5	

44K INHEX sockets


- for socket head screws
- Chrome Alloy Steel, chrome plated



Code	mm	L ₁ mm	L ₂ mm	d mm	Δg	g	
01120003	3	28	16	11.6	10	5	
01120004	4	28	16	11.6	10	5	
01120005	5	28	16	11.6	10	5	
01120006	6	28	16	11.6	10	5	
01120008	8	28	16	11.6	15	5	

44KTX Screwdriver sockets

- for inside TORX® screws
- Chrome Alloy Steel, chrome plated



Code	size	mm	L ₁ mm	L ₂ mm	d mm	Δg	g	
01350008	T8	2.3	28	16	11.6	10	5	
01350009	T9	2.5	28	16	11.6	10	5	
01350010	T10	2.7	28	16	11.6	10	5	
01350015	T15	3.3	28	16	11.6	10	5	
01350020	T20	3.8	28	16	11.6	11	5	
01350025	T25	4.4	28	16	11.6	11	5	
01350027	T27	5.0	28	16	11.6	11	5	
01350030	T30	5.5	28	16	11.6	12	5	
01350040	T40	6.6	28	16	11.6	12	5	

6,3
1/4"

DIN
3120

ISO
1174-1

3