





### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKD XCKP XCKT XCMD

Associated body	ZCMD41L1 ZCMD29L2 ZCD29M12 ZCP26 ZCP29 ZCMD41L5 ZCMD39L2 ZCT27P16 ZCMD69C12 ZCMD25L1 ZCMD61C12 ZCP31 ZCMD37L5 ZCMD81L2 ZCT25P16 ZCD25 ZCT26P16 ZCMD21L08R12 ZCT25N12 ZCT26N12 ZCD21 ZCT21P16 ZCMD81L5 ZCD37 ZCT25G11 ZCP39 ZCMD29C12 ZCT28P16 ZCP21M12 ZCT26G11 ZCD27 ZCMD25L5 ZCP21 ZCP37 ZCD28 ZCMD21L2 ZCMD21L08U78 ZCT21G11 ZCP25 ZCT21N12 ZCMD37L1 ZCD39 ZCMD61M12 ZCT28N12 ZCMD25L2 ZCD29 ZCD35 ZCMD81L1 ZCT28G11 ZCMD21C12 ZCMD29L5 ZCMD21L1 ZCMD21M12 ZCMD39L5 ZCP35 ZCMD37L2 ZCD21M12 ZCT27G11 ZCMD21L5 ZCP27 ZCP28 ZCMD39L1 ZCD26 ZCT27N12 ZCMD41L2 ZCD31 ZCMD29L1 ZCP29M12
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach, 2 directions

### Complementary

Switch actuation	By 30° cam
Positive opening	With

## Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901290469
Nbr. of units in pkg.	1
Package weight(Lbs)	0.04 lb(US) (0.02 kg)
Returnability	Yes
Country of origin	ID

## Packing Units

Package 1 Height	0.400 dm
Package 1 width	0.150 dm
Package 1 Length	0.150 dm

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------