

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0099990992](#)  
**Status:** **Active**  
**Overview:** [Mini-SPOX Wire-to-Board Connector System](#)  
**Description:** 2.50mm Pitch, Mini-SPOX PCB Header, Single Row, Vertical, Through Hole, Tin Plating, 8 Circuits, Bag, with Swaged PC Tails

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification 52641001-PS-000 (PDF)</a>
<a href="#">2D Drawing DXF (PDF)</a>	<a href="#">Product Specification PS-5264-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification SPK-5267-001-001 (PDF)</a>
<a href="#">2D Drawing (DXF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">3D Model (PDF)</a>	

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">5267</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Mini-SPOX Wire-to-Board Connector System</a>
Product Name	Mini-SPOX
UPC	800753629783

**Physical**

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	692.300/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5267 Series](#)

**Mates With**

Mini-SPOX Receptacle Housing [5264](#)

Termination Interface: Style

Through Hole

**Electrical**

Current - Maximum per Contact

3.0A

Voltage - Maximum

250V

**Material Info**

Engineering Number

5267-08A-X

**Reference - Drawing Numbers**

Packaging Specification

SPK-5267-001-001

Product Specification

52641001-PS-000, PS-5264-001-001

Sales Drawing

52670002-SD-000

This document was generated on 08/25/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**