

LED PIPE High OUTPUT

LED PIPE G2 L600 HIGH OUTPUT WW

0051042



Product features

- LED T5 replacement batten, high output range: more lumens per meter with efficiency up to 125 lum/watt, seamless linking (up to 10M), Ideal for direct lighting such as under cabinet or in kitchens, 150 degree beam angle, includes switch, includes 0.30m stripped cable, white polycarbonate body, includes standard and tilting brackets



PRODUCT OVERVIEW

Product name	LED PIPE G2 L600 HIGH OUTPUT WW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer
ETIM Class	EC000109
E-number SE	7505149
Warranty	3 years
Fixture luminous flux (lm)	900
Luminaire efficacy (lm/W)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	150
Photobiological Risk Group	RG0
Total power consumption (W)	9
Product Voltage (V)	72
Electrical protection	Class II
Dimmable	No
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288510422

DATA TABLE

General data

Product name	LED PIPE G2 L600 HIGH OUTPUT WW
Technology	LED
Housing	PC Polycarbonate
General application	Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25

LED PIPE High OUTPUT

LED PIPE G2 L600 HIGH OUTPUT WW

0051042

ETIM Class	EC000109
E-number SE	7505149
Warranty	3 years

Optical data

Fixture luminous flux (lm)	900
Luminaire efficacy (lm/W)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Beam Angle (°)	150
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	9
Mains voltage (V)	220-240V
Product Voltage (V)	72
Lamp power factor	0.9
Electrical protection	Class II
Dimmable	No
Drive current (mA)	125
Inrush Current (A)	2
Inrush Duration (µs)	50
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	16
Max. Luminaires per 13A C Breaker	21
Max. Luminaires per 16A C Breaker	25
Max. Luminaires per 20A C Breaker	25
Max. Luminaires per 10A B Breaker	10
Max. Luminaires per 13A B Breaker	13
Max. Luminaires per 16A B Breaker	16
Max. Luminaires per 20A B Breaker	20

Lifetime data

Lifespan L70 B50	30000
------------------	-------

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	600
Nominal Product Width (mm)	24
Nominal Product Height (mm)	35
Weight (kg)	0.178

Packaging

Single packaging type	Carton
-----------------------	--------

LED PIPE High OUTPUT

LED PIPE G2 L600 HIGH OUTPUT WW


0051042

Product EAN number	5410288510422
Packaging single length / height (cm)	4.1
Packaging single width (cm)	3.2
Packaging single depth (cm)	72.0
DUN14 (outer)	15410288510429
Units per outer package	20
Packaging outer length / height (cm)	74.0
Packaging outer width (cm)	18.5
Packaging outer depth (cm)	19.0

Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



TECHNICAL DRAWINGS

