

## ToLEDo Retro Candle Twister

ToLEDo RT CAND TW V4 CL 470LM 827 E14 SL

0027338



### Product features

- Perfect for decorative and general lighting applications and creates a warm ambience similar to traditional lamps
- The versatile ToLEDo Retro candle range is the ideal replacement for halogen and incandescent lamps and perfect for chandeliers and decorative applications
- Same look, size and functionality as incandescent lamps
- Omni-directional light distribution
- A++ energy rating
- Gives same sparkling light effect as the incandescent lamp
- Dimensionally identical to incandescent lamps - fits all fixtures
- Environment-friendly - no mercury and lower CO2 emissions



## PRODUCT OVERVIEW

Product name	ToLEDo RT CAND TW V4 CL 470LM 827 E14 SL
Technology	LED
Watt (Rated) (W)	4.5
Type	ToLEDo Retro Candle
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740642
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam Angle (°)	300
Wattage (W)	4.5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288273389

## DATA TABLE

### General data

Product name	ToLEDo RT CAND TW V4 CL 470LM 827 E14 SL
Technology	LED
Watt (Rated) (W)	4.5
Type	ToLEDo Retro Candle
Cap/Base	E14
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25

## ToLEDo Retro Candle Twister

ToLEDo RT CAND TW V4 CL 470LM 827 E14 SL

0027338

ETIM Class	EC001959
E-number FI	4740642
Warranty	3 years

### Optical data

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Beam Angle (°)	300
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	4.5
Equivalent watt (W)	40
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	2.6
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	38
Max. Luminaires per 16A C Breaker	62
Max. Luminaires per 20A C Breaker	77

### Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	97
Nominal Product Diameter (mm)	35
Weight (kg)	0.015

### Packaging

Single packaging type	Carton
Product EAN number	5410288273389
Packaging single length / height (cm)	10.6
Packaging single width (cm)	3.8
Packaging single depth (cm)	3.8
DUN14 (inner)	25410288273383
Units per inner package	6
Packaging inner length / height (cm)	15.0
Packaging inner width (cm)	11.1
Packaging inner depth (cm)	12.9

## ToLEDo Retro Candle Twister

ToLEDo RT CAND TW V4 CL 470LM 827 E14 SL

0027338

DUN14 (outer)	15410288273386
Units per outer package	60
Packaging outer length / height (cm)	56.9
Packaging outer width (cm)	31.9
Packaging outer depth (cm)	15.3

### Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

## TECHNICAL DRAWINGS

