

Adjustable clamps

Depressed centre



Version:

- Heat-treated steel
- Painted
- Single depressed centre



Art. no.	26138 080
Slot width	22 mm
Length	200 mm
Suitable cheese-head screw DIN 912	M20, M22
Slot length	70 mm
Clamping shoe height	30 mm
Clamping shoe width	60 mm
Height	27 mm
Width 3	30 mm
Height 2	24 mm
DIN	6316

EAN-Code

4020772071097