



2000
kWh/1000h

B
energy class

25
lumens/watt

Double Ended Quartzline

P2/27 FEX 230V

88482

Product information

Precision range of double ended Quartzline® lamps widely used in theatre and many other applications. A range from 350 W to 2,000 W with 3200K.

Application areas

 Theatre



Product data

Product Code	88482
Bulb Shape	Tubular
Bulb Diameter [mm]	26.5
Maximum Overall Length [mm]	143
Net weight per piece [g]	44
Gross weight per piece [g]	89
Brand	GE Lighting
Cap/Base	Rx7s

Performance data

Rated Lumens [lm]	50000
Weighted energy consumption [kWh/1000h]	2000.0
Energy efficiency class (EEC)	B
Rated Life [h]	300
Nominal correlated colour temperature (CCT) [K]	3200
Nominal lumens [lm]	50000

Electrical data

Rated power [W]	2000.0
Coil type	C8
Dimming Capability	Yes
Ballast Required	No
Nominal power [W]	2000.0
Nominal lamp voltage [V]	230

Logistic data

DUN Code	10043168884829
EAN Code	0043168884822
Pack Quantity	12
Inner pack type	BOX
Outer pack type	OUTER BOX
Layer quantity	144 EUR, 180 UK
Layer quantity EUR	144
Layer quantity UK	180
Pallet quantity EUR (PC)	1152
Pallet quantity UK (PC)	1440
Outer case size	350 x 190 x 134 (mm)
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[Entertainment Pocket brochure \(PDF\)](#)

[High-res images / Technical drawings \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)

Disclaimer

Special Purpose Lamp, Not suited for household illumination

