


7.62mm Header Straight Closed 15A Terminal Blocks

Specifications

| | |
|--------------------------|------------------------|
| Pitch: | 7.62mm |
| Type: | Straight, Closed-ended |
| Poles: | 2 to 12 |
| Rated Voltage: | See Table |
| Rated Current: | See Table |
| Operational Temperature: | -40°C to +105°C |
| Withstand Voltage: | 2500V AC for 60s |
| Insulation Resistance: | 500MΩ at 500V DC |
| Wave Soldering: | 260°C for 5s |
| Hand Soldering: | 350°C for 10s |





Colour and Materials


| | |
|-------------------|------------------|
| Housing Colour: | Green |
| Housing Material: | PA66 |
| Flame Retardancy: | UL94-V0 |
| Pin Header: | Tin-plated brass |

| Order Code | Poles | Order Code | Poles |
|------------|-------|------------|-------|
| 21-1873 | 2 | 21-1878 | 8 |
| 21-1874 | 3 | 21-2009 | 9 |
| 21-1875 | 4 | 21-1879 | 10 |
| 21-1876 | 5 | 21-2011 | 11 |
| 21-1877 | 6 | 21-1880 | 12 |
| 21-2008 | 7 | | |

| Standard | Rated Voltage | Rated Current |
|----------|---------------|---------------|
| UL | 300V | 15A |
| IEC | 400V | 20A |



Measurements are in mm unless stated otherwise.



For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact. Telephone our main office on **01206 838000** or email Sales@Rapidonline.com.

The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.

