


Part Number: 1921X00X

Type	Size	Rating	Description
LED	M14	-	LED Standard Panel Indicator

Dimensions (mm)



Part #.	Colour	Voltage $V_f$	Current (mA)	Intensity (mcd)
1921X000	Red	2.0	30mA max.	150 (20mA)
1921X001	Green	2.2	30mA max.	70 (20mA)
1921X002	Yellow	2.1	30mA max.	70 (20mA)
1921X003	Red	2.0	30mA max.	200 (20mA)
1921X00W	White	3.3	30mA max.	1000 (20mA)

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Storage temperature -25 °C to +80°C
- 3 Application temperature -20 °C to +60°C
- 4 Sealed to IP67 above panel when supplied gasket used
- 5 The plastic(polycarbonate) has limited chemical resistance
- 6 RoHS & REACH SVHC compliant