




## Material & Electrical:

<b>Shell:</b>	Steel zinc plated or tin-plated
<b>Current rating:</b>	5 Amp
<b>Dielectric strength:</b>	1000V for one minute
<b>Insulator resistance:</b>	1000MΩ min. at 500V DC
<b>Insulator:</b>	PBT and glass fibre reinforced UL-94-V0
<b>Temperature:</b>	-55°C to +105°C
<b>Contacts:</b>	Gold plated over nickel



Order code	Description	A	B	C	D
15-0500	9-way Solder Lug Male	30.81	24.88	16.92	19.28
15-0505	15-way Solder Lug Male	39.14	33.32	25.25	27.51
15-0510	25-way Solder Lug Male	53.04	47.04	38.96	41.30
15-0515	37-way Solder Lug Male	69.32	63.50	55.42	57.71
15-0525	9-way Solder Lug Socket	30.81	24.88	16.33	19.28
15-0530	15-way Solder Lug Socket	39.14	33.32	24.66	27.51
15-0535	25-way Solder Lug Socket	53.04	47.04	38.38	41.30
15-0540	37-way Solder Lug Socket	69.32	63.50	54.84	57.71