


ROLINE LineSecure III 3000 - Line Interactive UPS

Product No.	19.40.1125	
Manufacturer	ROLINE	Designed for Professionals
Manufacturer No.	19401125	



LineSecure UPS's work with the "buck & boost" line interactive technology; used when reliable protection against strong voltage fluctuations is essential. Protect against: power failure, power sag, power surge, under voltage, over voltage.

Product features:

- Compact, quiet, user friendly
- Desktop and 19" RM models
- Short circuit and overload protection
- AVR (Automatic Voltage Regulation)
- ABM (Automatic Battery Management) increases battery life up to 50%
- Telephone/Modem connections
- Shutdown software including License for 1 server
- Serial Port for advanced Power Management Software (incl, in content of delivery)
- UPS Management Software : Windows NT/ 2k / XP / 7 / 8 /Server 2003 / 2008 / 2012 x86/x64,
MAC OS X (Intel) 10.6.x, 10.7.x, 10.8.x Mountain Lion, 10.9.x MavericksMAC OS, LINUX
- Content: UPS, Cable set, Software CD

Technical specifications

Manufacturer	ROLINE
Product group	UPS
Product type	UPS Line Interactive
Colour	black

Scope of delivery	UPS, Software, Cable Set
Classification (IEC 62040-3)	VI-SS-333
UPS technology	Line Interactive
Power class	2000 ... 3000 VA
Output (VA/W)	1000 / 700
Efficiency	95 %
Backup time	3 min
Backup time full/half-load	3 / 6 min
Dimensions (HxWxD)	210 x 140 x 436 mm
Mounting form	Tower
Voltage (input)	230 V +- 15%
Voltage (output)	230 V
Frequency	50 Hz
Connector type (input)	cold connector IEC320 C14
Outputs	8
Connector type (output)	4x cold connector IEC320 C13
Phase in/output	230V/230V / 50Hz
Over current protection	EMI,- RFI-Filter
Max. quantity of delay expansion units	0
Delay expansion unit	--
Slots for adapter card	0
Slot for adapter card	--
Interface	USB, RS232
RS-232 Interface	Yes
USB 2.0 Interface	Yes
Hot swap batteries	No
Bypass	No

Additional over current protector	Telephone/Fax
Activity	Display
Activity LED	---
Activity Display	LCD
incl.Management Software	Windows
Internal cooling	Active, fan
Ambient temperature	0-40°C
Operating temperature min.	0 °C
Operating temperature max.	40 °C
Height	226 mm
Width	170 mm
Depth	450 mm
Weight	25.4 kg
Package weight (single piece)	30.5 kg