

# LED DRIVER 30 WATT CONSTANT VOLTAGE

## POWERPAX: LED-DR-12V-2500-30W

### Features:

- AC input 200-240 Vac 50Hz
- Class II
- Compact Plastic Low Profile enclosure
- 3 Year Warranty



### Description:

The Range of 30 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality plastic IP20 enclosure with covered input & output terminals suitable for general Indoor LED applications

Specification	
Part Number	LED-DR-12V-2500-30W
Output Voltage	12V
Output Current	2.5A
Rated Power	30W max
Dimensions	159.9 x 57.8 x 18mm
Input Voltage Range	200-240V
Input Voltage Frequency	50Hz
Power Consumption Without Load	PF≥0.9W
Protections	Open Circuit Short-Circuit Over Load Over Heat
Ta	45°C
Tc	80°C
MTBF	30000 Hours.
EMI emission	IEC55015
EMS Immunity	EN61000-3-2, EN61000-3-3, IEC61547
Safety Standards	IEC61347-1, IEC61347-2-13

### General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

# LED DRIVER 30 WATT CONSTANT VOLTAGE

POWERPAX: LED-DR-12V-2500-30W

---

## Diagrams



---

### General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

## POWERPAX

TT Electronics IoT Solutions Ltd  
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK  
t: +44 (0) 1429 852 500