

Nuts

For ‚Rhombus‘ T-grooves



Application:

For inserting sliding block from above through the neck of the T-groove.

Version:

- Tempered
- The reduced contact surface in the T-groove results in a lower load capacity compared with comparable DIN 508 sizes.



Art. no.	26194 070
Nominal dimension of groove	22 mm
Slot nut width	21.7 mm
Thread dimension	M20
Height	28 mm
Slot nut height	14 mm
Length	35 mm
Property class	6

EAN-Code

4020772080303