

Pitbull tensioning clamps

Application:

For clamping workpieces.

Execution:

- Clamp with blunt edge
- Pitbull tensioning clamps for fixture plates

Advantage:

- Space-saving, ideal for multiple clamping
- Compact design allows machining on multiple sides
- Secure clamping thanks to high clamping force
- Strong pull-down force, which enables precise machining
- Thanks to its low height, no troublesome edges for tools

Delivery:

Ref. no. 26



Art. no.	26222 303
Brand	IBT
Manufacturer Part Number	X56030
Size	3
Distance	5.1 mm
Length	12.7 mm
Width	12.7 mm
Thickness	2.6 mm
Tension force	6.6 kN
Width 2	4.8 mm
Material of clamping clip	Steel
Tightening torque	5.6 Nm
Max. clamping width	0.4 mm
Thread dimension	M4
Number of pieces in assortment/set	8 PCS
Gross Weight	0.064 kg
Product Group	278