

Micrometer

With cylindrical and spherical measuring faces

Mitutoyo

Application:

For measuring e.g. curved surfaces and wall thicknesses of pipes, bearings, rings, etc.

Version:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Friction coupling for consistent, repeatable measuring force

Delivery:

Includes box, setting standard (from 25 mm), adjustment wrench



Art. no.	32016 620
Min./max. length measuring range	0-25 mm
Vernier scale	0.01 mm
Measuring surface depth	12.7 mm
Measuring spindle increments	0.5 mm
Measuring surface width x Measuring surface depth	4.7 x 12.7 mm
Spindle clamping	Yes
Error limit	3 µm
Display	Nonius
Calibration Group	D
Type	C – with cylindrical anvil
Min./max. measurement force	3-8 N

EAN-Code

4946368011189