

Articulated lamp with bulb E 27 socket

Application:

For workstations and machines.

Execution:

- Voltage 230 V, 50 Hz, noise suppressed
- With E27 holder for impact-resistant bulbs up to 100 W, ECO halogen A lights up to 70 W or 15-W energy-saving lights
- Colour: aluminium silver, similar to RAL 9006

Delivery:

With 1.5-m cable and Schuko plug, screw-on flange, excluding bulb



Art. no.	56871 505
Brand	SIS LIGHT SOLUTIONS
Manufacturer Part Number	711.95.06
Power rating	70 W
Arm length	900 mm
IP protection class	IP 20
Gross Weight	2.000 kg
Product Group	5ID

EAN

4003682711062