

# MSR Gold™ FastFit

## MSR Gold™ 700 FastFit 1CT



All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

## Product data

### • General Characteristics

System Description	FastFit
Cap-Base	PGJX50
Cap-Base Information	PGJX50
Execution	-
Operating Position	any
Main Application	Entertainment
Life to 50% failures	750 hr
EM	

### • Light Technical Characteristics

Color Rendering Index	80 Ra8
Color Temperature	6000 K
Color Temperature Technical	6000 K
Chromaticity Coordinate X	327 -
Chromaticity Coordinate Y	336 -
Luminous Flux Lamp EM	45500 (min), 50000 (nom) Lm
Luminous Efficacy Lamp EM	71 Lm/W

### • Electrical Characteristics

Lamp Wattage	700 W
Lamp Wattage Technical	700 W
Lamp Current	10.2 A
Ignition Supply Voltage	198 (min) V

Dimmable	Yes
----------	-----

### • Luminaire Design Requirements

Pinch Temperature	500 (max) C
Bulb Temperature	950 (max) C

### • Product Dimensions


Overall Length C	112 (max) mm
Diameter D	23.2 (max) mm
Width F	50 mm
Light Center Length L	64 (min), 65 (nom), 66 (max) mm
Arc Length O	3.8 mm

### • Product Data

Order code	928106005115
Full product code	928106005115
Full product name	MSR Gold™ 700 FastFit 1CT
Order product name	MSR Gold 700 FastFit 1CT/4
Pieces per pack	1
Packing configuration	4
Packs per outerbox	4
Bar code on pack - EAN1	8718291221197
Bar code on outerbox - EAN3	8718291221203
Logistic code(s) - 12NC	928106005115
Net weight per piece	0.100 kg


# PHILIPS

Dimensional drawing




MSR Gold™ 700 FastFit 1CT

Product	A (Min)	A (Norm)	A (Max)	C (Max)	D (Max)	D1 (Norm)	F (Min)	F (Norm)	F (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
MSR GOLD 700 FastFit	-	-	-	112	23.2	-	-	50	-	64	65	66	3.8




PGJX50

Photometric data



MSR Gold™ 700(2) FastFit



MSR Gold™ 700(2) FastFit



© 2015 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2015, March 5  
data subject to change