

# NYS229L

2 pole open 1/4" jack, 2 contacts, with longer threaded nose, washer and nut, panel thickness 6.5 mm, with 0.205" faston tabs



## Technical Information [▼hide](#)

<b>Product</b>	
Title	NYS229L
<b>Electrical</b>	
Dielectric strength	Diel 0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
<b>Mechanical</b>	
Insertion force	≤ 20 N
Withdrawal force	≥ 10 N
Lifetime	1000 mating cycles
Panel thickness	3.5 mm
<b>Material</b>	
Insulation	Insulation board
<b>Environmental</b>	
Temperature range	-20 °C to +70 °C