


REV.	DATE	DESCRIPTION
A	01/10/04	UPDATE DRAWING FORMAT



NOTE:
 1. CRIMPED FERRULE
 HEX CRIMP SIZE .319"
 2. CRIMPED CONTACT PIN
 HEX CRIMP SIZE .068"

NO.	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	APPROVALS	DATE	PART DESCRIPTION							
8						DRAWN	G.R.S.	01/10/04	<p style="text-align: center;">Amphenol Connex</p> <p style="text-align: center;">BNC R/A CRIMP PLUG (FOR RG-6/U CABLE)</p> <p style="text-align: center;">PART NO. 112540</p>						
7						CHECKED									
6	FERRULE	COPPER	NICKEL	1		ISSUED									
4	CONTACT PIN	BRASS	GOLD	2		SHEET	1 OF 1								
3	CONTACT PIN	PHOS. BRONZE	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1											
1	BODY	BRASS	NICKEL	1											
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/112/112540.DWG	DWG. NO.		112540.DWG	REV.	A	SIZE	A	SCALE