



PLUG-IN RELAY COMPACT UNIT AC 24V, 1 CO CONTACT LED MODULE RED STANDARD PLUG-IN SOCKET 5 MM PINNING

Figure similar

General technical data:		
Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
Type of voltage		AC
Control supply voltage		
• with AC		
— at 50 Hz Rated value		
— minimum	V	24
— maximum	V	24
— at 60 Hz Rated value		
— minimum	V	24
— maximum	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		1
Operating current of the auxiliary contacts		
• at AC-15		
— at 230 V	A	3
Design of the switching function positively driven		No
Switching behavior		monostable
Mechanical data:		
Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled

Product component Plug-in socket		Yes
Width	mm	15.5
Height	mm	71
Depth	mm	78

Certificates/ approvals:

General Product Approval	other
--------------------------	-------

[Declaration of Conformity](#)



Further information

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:RT3A4R24>

Information- and Downloadcenter (Catalogs, Brochures,...)


<http://www.siemens.com/industrial-controls/catalogs>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:RT3A4R24>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:RT3A4R24&lang=en



last modified:

15.01.2015