



PRODUCT-DETAILS

TY225-50-100

CBL TIE 50LB 9IN NATURAL NYLON



General Information

Extended Product Type	TY225-50-100
Product ID	7TCG054360R0231
EAN	5414363061342
Catalog Description	CBL TIE 50LB 9IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 215mm (8.46 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1.3mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), 100 Pack

Ordering

EAN	5414363061342
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.002 lb .907 g
--------------------	-------------------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	1 in 25 mm

Package Level 1 Height	5 in 127 mm
Package Level 1 Depth / Length	15 in 381 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	10.17 in 258 mm
Package Level 2 Height	14 in 356 mm
Package Level 2 Depth / Length	19.75 in 502 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	2.25 in 57.15 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Tensile Strength	50 lb 222 N
Thickness	0.05 in 1.3 mm
UPC	786210698014

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY225-50-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY225-50-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

