

## Rotational field and phase tester

TRITEST® easy

**BENNING**

### Application:

For quick and easy phase testing on sockets, branches, switches and lamps

### Version:

- Rotational field testing via green/red LED probe tip (right-hand/left-hand)
- LED blink frequency and signal tone frequency proportional to voltage level
- Capacitive measurement process requires no current flow

### Advantage:

- Simple testing of rotational field direction (L1-L2-L3) in alternating current networks using illuminating green LED probe tip = right-hand field
- illuminating red LED probe tip = left-hand field

### Delivery:

Includes Batteries, pen clip



<b>Art. no.</b>	<b>75018 110</b>
<b>Display</b>	LED, Audible
<b>Min./max. voltage range AC</b>	200-1000 V/AC
<b>Overvoltage protection category</b>	CAT IV/600 V, CAT III/1000 V
<b>Min./max. frequency</b>	45 / 65 Hz
<b>Phase-sequence test</b>	Yes
<b>Phase sequence test</b>	Yes

### EAN-Code

4014651200517