IDEAL 1

max.
12
sheets

24 cm

Attractively designed deskside shredder with innovative features.

Level P-5 2 x 15 mm particle cut


Sheet capacity*: 10-12 | 8-10



Technical specifications

Volume	25 litres (shred bin)
Power	230 V / 50 Hz**
Motor capacity	390 Watt single phase motor

** other voltages available



Dimensions	600 x 410 x 240 mm (H x W x D)
Weight	23,5 kg
ID-No.	11241001

GS certificate-No. DP 10034

Product characteristics

State-of-the-art shredder with ageless design and attractive metal housing. SPS (Safety Protection System): patented, electronically controlled safety flap in the feed opening as additional safety element; EASY-SWITCH – intelligent control element indicating the operational status of the shredder with back-lit symbols; automatic reverse and power cut-off (avoids paper jams); automatic stop if the shred bin is full; electronic door protection via a magnetic switch; double motor protection; energy saving mode. Photo cell controlled automatic start and stop. Quiet, powerful and energy-efficient single phase motor. High-quality, paper clip proof cutting shafts from special hardened steel with lifetime guarantee. Lightweight shred bin from impact-resistant plastic.









^{*} A4 paper 70 g/m² | 80 g/m²

IDEAL 1

Features



Robust and durable: high-quality paper clip proof cutting shafts with lifetime guarantee under conditions of fair wear and tear.



EASY-SWITCH

Ease of operation: intelligent multifunction switch element with integrated optical signals indicating the operational status.



PATENTED SAFETY FLAP

Extremely safe: electronically controlled safety flap in the feed opening to keep fingers, ties or other objects away from the cutting shafts.



AUTOMATIC STOP

Automatic stop if the shred bin is full and electronic door protection via a magnetic switch.



















certificate

no. **DP 15044** dated 2015-03-25



<u>Translation</u> In any case, the German original shall prevail.

GS Certificate

Name and address of the Krug & Priester GmbH & Co. KG holder of the certificate: Simon-Schweitzer-Straße 34

(customer) 72336 Balingen

Product designation: file shredder

Type: 11231001, 11236001, 11240401, 11241001, 11244501, 11246501,

11250203

Testing based on: DIN EN 60950-1:2014 Information Technology Equipment – Safety –

Part 1: General requirements

EN 60950-1:2006+A11:2009+A1:2010+A12:2011 Information Technology Equipment – Safety – Part 1: General requirements

IEC 60950-1:2005+AMD1:2009+AMD 2:2013 Information Technology Equipment – Safety – Part 1: General requirements EN 1010-1:2004+A1:2010 Safety of machinery – Safety requirements

for the design and construction of printing and paper converting

machines; Part 1: common requirements

Test report: 612.17 - So/Ho

A 14199

Produktgruppe: 001.1001

Further details:

The type tested meets the requirements specified in article 21 para. 1 of the German Product Safety Act. The holder of the certificate is entitled to affix the GS mark shown overleaf to the products complying with the type tested. At that, the holder of the certificate shall observe the conditions specified overleaf.

The present certificate including the right to affix the GS mark is valid until: 2020-03-24

Further provisions concerning the validity, the extension of the validity and other conditions are laid down in the Rules of Procedure for Testing and Certification.



Dipl.-Ing. Andreas Vogl

