



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/1 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR $Gold^{\mathsf{TM}}$ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information				
Cap-Base	PGJX28 [PGJX28]			
Operating Position	UNIVERSAL [Any or Universal (U)]			
Main Application	Entertainment			
Life to 50% Failures (Nom)	750 h			
System Description	MiniFastFit			
Light technical				
Color Code	1			
Luminous Flux (Nom)	53400 lm			
Chromaticity Coordinate X (Nom)	328			

Chromaticity Coordinate Y (Nom)	335
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	76.3 lm/W
Color Rendering Index (Nom)	73
Operating and electrical	
Power (Nom)	700 W
Lamp Current (Nom)	10.2 A
Ignition Supply Voltage (Min)	198 V


Datasheet, 2022, January 14 data subject to change

MSR Gold™ MiniFastFit (Touring/Stage)

Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Cap-Base Information	PGJX28
Luminaire design requirements	
Bulb Temperature (Max)	950 ℃
Pinch Temperature (Max)	500 ℃
Product data	
Full product code	871829169663600

Order product name	MSR Gold™ 700/1 MiniFastFit 1CT/4
EAN/UPC - Product	8718291696636
Order code	928197405115
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928197405115
Net Weight (Piece)	0.052 kg

Dimensional drawing



MSR Gold™ 700/1 MiniFastFit 1CT/4

Product	D	0	L	L	L	С	F	F	F
	(max)		(min)	(max)		(max)	(max)		(min)
MSR Gold™	23.2	3.8	55 mm	57 mm	56	112 mm	36.5	36	35.3
700/1	mm	mm			mm		mm	mm	mm
MiniFastFit									
1CT/4									

