





RoHS

THIS IS A RoHS COMPLIANT COMPONENT/PRODUCT.



PC Board Layout Component Side Shown



△ X 1		ADD NEW P/N	KARL	092413
△ X 1		MODIFY NOTE	ROCK	082312
△ X 1		ADD PART NO.	ROCK	010912
△ X 2		DESIGN MODIFY	YANG	090408
△ X 1		ADD PART NO.(3)	SAIL	022008
△ X 0	000000	NEW DESIGN	Frank	112007
MARK	ECN-NO.	REVISION RECORD	DRAWN	DATE

encitech	UNLESS OTHERWISE SPECIFIED TOLERANCE		SCALE	CHECKED
	Dimension Range	Tolerance	2:1	
	X.X	±0.20	UNIT	APPROVED
	X.XX	±0.15	mm	
X.XXX	±0.10	SIZE	A3	SHEET 1/2
ANGLE	±5°			
Material/Plated/Notes	NAME			
SEE NOTE	CAT.5e SIDE ENTRY JACK W/ SHIELD			
Tooling No.	PART NO.	SEE NOTE	REV.	
	DOC. NO.		F	



Notes :

Electrical :

- 1. Voltage Rating :125 Vac.
- 2. Current Rating : 1.5 A
- 3. Contact Resistance : 60 MilliOhms Max.
- 4. Insulation Resistance : 1000 Megohms Min. @ 500 Vdc.
- 5. Dielectric Strength : 1000 Vac 60Hz, 1Min.

Mechanical :

- 1. Shield : t=0.25mm Brass C2680 H, Plated 30u"~50u" Nickel.
- 2. Housing : High Temp. UL 94V-0.
- 3. PCB : FR-4, 0.5mm Thickness.
- 4. Contact : Phosphor Bronze t=0.35mm. Selective Gold Plating Over 50u"Nickel.
- 5. Operating Life : 750 Cycles Min.

Environmental :

- 1. Storage : -40°C To +85°C.
- ▲ 2. Operation : -40°C To +85°C.

Mates With Modular Plug Conforming To FCC PART 68, Subpart F.

ORDERING INFORMATION:

PART NUMBER	PRODUCT CODE	CONFIGURATION
3259-0016-01	RJJS-88-I2I-E9H-032	6U" GOLD PLATING, WITH EMI TABS
3259-0016-02	RJJS-88-I22-E9H-032	6U" GOLD PLATING, WITHOUT EMI TABS
3259-0016-03	RJJS-88-I4I-E9H-032	30U" GOLD PLATING, WITH EMI TABS
3259-0016-04	RJJS-88-I42-E9H-032	30U" GOLD PLATING, WITHOUT EMI TABS



Frequency MHz	Near-End Cross Talk dB, Min.	Return Loss dB, Min.	Attenuation dB, Max.
1.0	65	30	0.1
4.0	65	30	0.1
8.0	64.9	30	0.1
10.0	63	30	0.1
16.0	58.9	30	0.2
20.0	57	30	0.2
25.0	55	30	0.2
31.25	53.1	30	0.2
62.5	47.1	24.1	0.3
100.0	43	20	0.4

MARK	ECN-NO.	REVISION RECORD	DRAWN	DATE
▲ X1		ADD NEW P/N	KARL	092413
▲ X1		MODIFY NOTE	ROCK	082312
▲ X1		ADD PART NO.	ROCK	010912
▲ X2		DESIGN MODIFY	YANG	090408
▲ X1		ADD PART NO.(3)	SAIL	022008
▲ X0	0069000	NEW DESIGN	Frank	112007

	UNLESS OTHERWISE SPECIFIED TOLERANCE		SCALE	CHECKED
	Dimension Range	Tolerance	2:1	
	X.X	±0.20	UNIT	APPROVED
	X.XX	±0.15	mm	
X.XXX	±0.10	SIZE	A3	SHEET 2/2
ANGLE	±5°			
Material/Plated/Notes	NAME			
SEE NOTE	CAT.5e SIDE ENTRY JACK W/ SHIELD			
Tooling No.	PART NO.	SEE NOTE	REV.	F
	DOC. NO.			