

Item no.: 2348261

## Data Sheet

### Inductive proximity sensor M12, 4mm, plug



#### Technical data

Operating voltage: 6 - 36V DC

Outputs: PNP

Connector: M12 (4-pin)

Material: Brass

Switching distance (max.): 4mm

Length: 61.8mm

Switching frequency: 1800Hz

Operation temperature: -30°C~ +80°C

Storage temperature: -30°C~ +80°C

Humidity: 35 to 95% RH

IP67

#### Wiring diagram

