

FEATURES

- Single pedal foot operated switches
- Durable and reliable with steel housing for long life
- Latching and non-latching versions available
- Rated 250Vac/30Vdc at 3A
- Incorporates non-slip base pad and footpad
- Comes with 2m cable

RS PRO General Purpose Latching Foot Switch - Mild Steel Case Material, Single Pole Single Throw (SPST), 3 A Contact

RS Stock No.: 316-939



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO general purpose light duty foot switch with SPDT (Single Pole Double Throw) Contacts. Foot switches are commonly used on large machinery where hand operated switches are a safety concern. This foot controller pedal is black and grey in colour and ideal for various applications.

This range includes:

316-901 - Momentary and non-latching

316-939 - Latching and maintained

General Specifications

Contact Configuration	Single Pole Single Throw (SPST)
Switch Operation	Latching
Case Material	Mild Steel
Switch Environment	General Purpose
Contact Material	Silver
Colour	Black, Grey
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	Supplied with 2metres of 4 core cable

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Voltage Rating (DC)	30V
Contact Current Rating	3A

Mechanical Specifications

Length	90mm
Height	24mm
Dimensions	90mm x 66mm x 24mm
Width	66mm

Operation Environment Specifications

Operating Temperature	-10 to 40°C
------------------------------	-------------


Protection Category

IP Rating	IPX2
------------------	------

Approvals

Standards Met	2014/35/EU, EN 60950
Compliance/Certifications	EN 61058-2-1; EN 61058; EN 60601-1; EN 60950, RoHS





Outline Dimensions

