

# Stranded wire Copper LSZH

Stranded Wires with PVC Insulation, H05Z-K, RND



## FEATURES:

For use in pipes or ducts and internal wiring of appliances with maximum operating temperatures of 90°C

The cables produce no corrosive gases when burnt

Class 5 flexible copper conductor according to

BS EN 60228

## SPECIFICATION:

Wire Code	H05Z-K
Cable type	Stranded
Shielding	unshielded
Conductor	Copper
Halogen-free	No
Conductor insulation	LSZH
Original packaging	100 m
Rated voltage	300/500 V
Temperature range	-25...+90 °C

## PRODUCT RANGE:

Art. Nr.	Colour	Cross-section	∅ Sheath
RND 475-00167	black	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00168	blue	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00169	brown	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00170	green/yellow	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00171	grey	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00172	red	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00173	white	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00174	yellow	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00175	orange	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00176	pink	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00177	violet	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00178	green	0.50 mm <sup>2</sup>	2.4 mm
RND 475-00179	black	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00180	blue	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00181	brown	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00182	green/yellow	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00183	grey	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00184	red	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00185	white	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00186	yellow	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00187	orange	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00188	pink	0.75 mm <sup>2</sup>	2.8 mm

<b>Art. Nr.</b>	<b>Colour</b>	<b>Cross-section</b>	<b>∅ Sheath</b>
RND 475-00189	violet	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00190	green	0.75 mm <sup>2</sup>	2.8 mm
RND 475-00191	black	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00192	blue	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00193	brown	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00194	green/yellow	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00195	grey	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00196	red	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00197	white	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00198	yellow	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00199	orange	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00200	pink	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00201	violet	1.00 mm <sup>2</sup>	2.9 mm
RND 475-00202	green	1.00 mm <sup>2</sup>	2.9 mm