

S.13 S - 1/2" metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Supplied on metal rack. Ref S.40E (8 --> 16 mm) and Ref S.41E (17 --> 24 mm).

A [mm]:	13
d [mm]:	22,8
d1 [mm]:	18,9
L [mm]:	36
L1 [mm]:	10,4
12-Point [mm]:	12
[g]:	55

