




ASTGH080MSS0005H08

Connection technology



Product characteristics

Cable plug

M12 connector

Free from halogen

Electrical data

Electrical design

AC/DC

Operating voltage [V]

30 AC / 36 DC

Environment

Ambient temperature [°C]

-25...80

Protection

IP 67

Mechanical data

Design

straight

Material body

PUR

Material nut

Brass; nickel-plated

Tightening torque for knurled nut [Nm]

0.7...0.9

Weight [kg]

0.31

Electrical connection

Connection

PUR cable / 5 m; 8 x 0.25 mm<sup>2</sup>; Ø 6.8 mm; halogen-free

Sheath colour

black

**Wiring**

Core colours

BK black

BN brown

BU blue


GY grey

PK pink

OG orange

VT lilac

WH white



1	BN
2	WH
3	BU
4	BK
5	GY
6	PK
7	VT
8	OG

Colours to DIN EN 60947-5-2

Remarks

Pack quantity [piece]

1